

VERSION 2.1
MARCH 27 2017
ECEN 390
RX AMPLIFIER

CURRENT GAIN: 10,000
CAN BE INCREASED BY
LOWERING EMITTER RESISTORS
RAISING COLLECTOR RESISTORS
ON STAGES 1 AND 3

SOLDER RESISTOR AND DIODE
TOGETHER BEFORE INSERTION

PUT BOTH CAPACITORS
IN THE SAME HOLES,
IN PARALLEL

Designer: Jakob Kunzler

